


FOR COMPLEX MIXTURE ANALYSIS

CHARACTERISTICS

- ▶ Widely tunable DFB source (~80cm⁻¹)
- ▶ Large molecule detection, multispecies sensing and mixture analysis
- ▶ Starter kit available including lab electronics
- ▶ Full semiconductor solution
- ▶ No moving parts

SPECIFICATIONS



Type	multiMir-QCW multiMir -CW
Peak emission wavelength	between 3 and 12 μm
Operating temperature typ.	room temperature
Tunable range typ.	> 30 cm ⁻¹
Output power typ.	1-10 mW
Side-mode suppression ratio	30dB
Cooling system required	QCW : air CW: water or air
Package	Custom Butterfly package 50 pins

www.Auniontech.com