

RIGI-M2 Camera



Uncooled real-time THz imager



- Beam profiling
- Non-destructive testing
- Imaging systems
- Quality control
- Security and surveillance
- Optical alignment

Image using QCL THz source

Frequency: 4.6 THz
Power: 0.6 μ W
Integration time: 50 μs

• Acquisition: Single shot

	ltem	General Specifications	
	Detector	Uncooled FPA THz micro-bolometer array	
	Pitch	17 μm	
	Array size	640 x 480 pixels	
	Active area	10.9 x 8.2 mm	
	Operating fr	equency 0.1 - 20 THz	
	Pixel NEP	< 1.5 pW/√ Hz at 4.6 THz	
	Operating te	mperature -40 °C to 65 °C	
	Software	Included and adaptable upon request	

Compatible with most terahertz sources

1. Broadband terahertz sources

- Broadband plasma based source
- Organic crystal high power spectrometer
- Lithium Niobate crystal high power spectrometer
- ZnTe crystal based linear spectrometer
- Photoconductive switch oscillator based source
- Commercial time domain spectrometer

2. Narrowband terahertz sources

- OCL based source
- Solid state sources
- Crystal based DFG source
- CO2-based DFG source

E-Mail: info@auniontech.com Website: www.auniontech.com