

TECHNICAL DATA


40138

CYLINDRICAL HELIUM-NEON LASER SYSTEM

Wavelength	1.15 μm /3.39 μm
Minimum Output Power	2.0 mW/3.0 mW
Power 3 Seconds After Turn-On	> 75%
Polarization	Linear > 500:1
Mode Structure	TEM ₀₀ > 99%
Beam Diameter	0.90 mm (1.15 μm)
Beam Divergence	1.62mrad (1.15 μm)
Beam Diameter	1.55 mm (3.39 μm)
Beam Divergence	2.78mrad (3.39 μm)
Longitudinal Mode Spacing	316 MHz
Beam Drift After 20 Minute Warm-Up	< 0.2 mrad
Long Term Beam Drift	< 0.05 mrad
Noise (30 Hz - 10 MHz)	< 20% rms
Starting Voltage	< 10 kVDC
Operating Voltage	2800 VDC
Series Resistors in Housing	94 K Ω
Operating Current	6.50 mA
Shock	15 g for 11 msec
Laser Head Weight	750 grams
Dimensions	
Length	533.4 \pm 1.0 mm (21.00 \pm 0.04")
Diameter	44.5 \pm 0.5 mm (1.75 \pm 0.02")
Maximum Output Power (1.15 μm)	5.0 mW
Maximum Output Power (3.39 μm)	5.0 mW
CRDH/CE Classification	IIIb/3B
Recommended Power Supply	32882
Replacement Laser Head	30615

ENVIRONMENTAL SPECIFICATIONS

	<u>Operating</u>	<u>Non-Operating</u>
Temperature	-20 - +70° C	-40 - +80° C
Humidity	\leq 80%	\leq 95%
Altitude	0-3,000 meters	0-6,000 meters



5505 Airport Boulevard Boulder, Colorado 80301

Phone - (303) 938-1960 Fax - (303) 447-3279